

LEDBHO9WN

7W – 700lm LED Energy Saver Bulkhead Light – Oval

Features & Benefits

- Oval LED Bulkhead Light
- A powerful and energy saving alternative to standard bulkhead lights
- Wide light diffusion pattern
- Robust die cast housing with tough polycarbonate lens suitable for industrial, commercial and home installations
- IP65 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class I
Operating Temperature	-10°C to +40°C
Ingress Protection Rating	IP65
Wattage	7
Beam Angle	120°
Energy Efficiency	Class F
Energy Usage	7KwH/1000H
Lumen output (lm)	700

Data sheet

LEDBHO9WN

Light / LED Lighting

Colour Temperature (K)	5000
LED Type	SMD (On LED Plate)
Mounting Hole Centres (mm)	124
Multiple Unit Support	Yes
Cable Entry(s)	Back Entry, Side Entry (Lip In Housing)

General

Weight (g)	278
Height (mm)	155
Width (mm)	100
Depth (mm)	52
Body Construction	Polycarbonate (Front Cover), Aluminium (Body)
Product Colour	Silver
Accessories (Included)	Fittings
EAN Number	5012483015650
Guarantee Period	3 Years

Line Diagrams

