



138A - Nylon strap wrenches



Description:

- Capacity: 0 to 165 mm.
- Body in aluminum alloy.
- High strength nylon strap.



	A [mm]	Length L [mm]	Length L1 [mm]	Thickness E [mm]	Weight [g]
138A.17	60.0	300.0	450.0	42.0	280.0
138A.30	125.0	300.0	760.0	42.0	290.0
138A.48	165.0	300.0	1200.0	42.0	310.0