



3250
LUMEN



2-64H
RUNTIME



60M
RANGE



IP65
IP RATING

NEW CRI-3250 - RECHARGEABLE HIGH CRI INDUSTRIAL SITE LIGHT

- Ultra bright 3250 lumen 30W COB LED
- High CRI 96+ coloured COB LED
- Colour temperatures from 2700k - 6500k
- Easy twist switch to change colour temperature
- Memory function - remembers last colour used
- Easy twist smooth dimming switch
- Dual power - rechargeable and mains
- 2A USB power bank for charging devices
- Super tough nylon & aluminium construction
- Built-in aluminium heat sinks
- Glow-in-the-Dark strip around reflector for extra visibility
- 170° Rotating stand with 4 strong magnets
- Adjustable head to change light angle
- Mains multi-country charger/power lead included

BATTERY 11.1v 5200mAh Li-Ion Battery
WEIGHT 1500g
DIMENSION 243 x 236 x 125mm



MAGNETIC ROTATING BASE

