



NEW HL-8R - SENSOR DUAL BEAM HEADTORCH

USB
TYPE-C



RUBBERISED HEAD BRACKET



475
LUMEN



4-35H
RUNTIME



90M
RANGE



IP65/IPK07
IP RATING

- 475 Lumen 6500K white SMD LEDs
- 2 x Side SMD LEDs for wide flood lighting
- 250 Lumen SMD LED for long distance spot beam
- Intelligent sensor mode for hands-free operation
- Super tough construction - IK07 shock resistant
- IP65 dust & water resistant
- 60° Rotational head
- Fully adjustable non-slip silicone lined headband included

- Red-to-Green charging indicator light
- Fast 1A USB-C rechargeable - 2 ½ hours charge time
- 1m charging cable included

BATTERY 3.7v 1500 mAh Li-Polymer Rechargeable Battery

WEIGHT 111g

DIMENSION Headtorch: H 47.5 x W 78.5 x D 46mm