

TPC 342912



Sample image

Order symbol : TPC 342912

Product nr : 5824004

Description : Enclosure, PC



Remarks : Grey cover

EAN : 6418074086877

Including :

El. number :

- Finland :
- Denmark :
- Sweden :



Dimensions :

Height

Width

Depth

Accessories :

mm :	344	289	117
inch :	13.54	11.38	4.61

Materials :

Material :	Polycarbonate
Base colour :	
Cover colour :	
Gasket material :	

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

MP 3429	Mounting plate, for enclosures: (315 x 265 x 0)
ARH 2328	DIN-35 Mounting rail, for enclosures: (260 x 35 x 1)
FP 10674	Wall fastening lug (2 pcs) incl. screws
DR 316	DIN-35 Mounting rail, for enclosures: (316 x 35 x 1)

Rating :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	-
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

Certificate FI 40343