

# PC 36/31-C3



Sample image

**Order symbol :** PC 36/31-C3

**Product nr :** 7520032


**Description :** Enclosure, PC

**Remarks :** With aluminium front plate

**EAN :** 6418074005861

**EI. number :**

- Including :**
- Finland : 3420836
  - Denmark : 8212016693
  - Sweden :



<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	383	316	134
inch :	15.08	12.44	5.28

#### **Materials :**

Material :	Polycarbonate
Base colour :	
Cover colour :	
Gasket material :	Polyurethane

#### **Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

#### **Accessories :**

FP 36/31	Front plate (aluminium), for enclosures: (353 x 223 x 1)
MP 36/31	Mounting plate, for enclosures: (345 x 258 x 1)

#### **Rating :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

#### **Certificates :**

SGSFIMKO\_CARDpc