

# CAB PC 203018 G3B

**FIBOX**  
Enclosing innovations



Sample image

**Order symbol :** CAB PC 203018 G3B

**Product nr :** 8113334

**Description :** Cabinet, PC, Grey door


**Remarks :** Lock on the short side

**EAN :** 6418074012586

**El. number :**

- Finland :
- Denmark : 8212019807
- Sweden :

**Including :** Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.



<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	200	300	180
inch :	7.87	11.81	7.09

## **Materials :**

Material : Polycarbonate

## **Accessories :**

MB 12225 AL	Swing door set
EKIV 27	DIN-35 Mounting rail, for enclosures: (266 x 35 x 1)
DRF 23	DIN rail frame set, for enclosures:
FP A 23	Swing-out door/Front plate (aluminium), for enclosures: (168 x 268 x 1)

Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

EKIV 17	DIN-35 Mounting rail, for enclosures: (166 x 35 x 1)
---------	---

EKIV 23	Mounting plate, for enclosures: (170 x 270 x 1)
---------	--

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

**Rating :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

**Certificates :**

Certificate FI 40854