

CAB PC 403018 T



Sample image

Order symbol : CAB PC 403018 T

Product nr : 8113050

UL Code : 8143050

UL Name : UL CAB PC 403018 T

Description : Cabinet, PC, Smoked transparent door


Remarks : Latches on the long side

EAN : 6418074020215

EI. number :

- Finland : 3424164
- Denmark : 8212020252
- Sweden : 2539945

Including : Cabinet base. door with PUR gasket. latches. screws for mounting plate/ DIN-rail and corner plugs.



Dimensions :	Height	Width	Depth
mm :	400	300	180
inch :	15.75	11.81	7.09

Materials :

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey

Accessories :

DRF 43/44	DIN rail frame set, for enclosures:
MB 12225 AL	Swing door set
EKIV 37	DIN-35 Mounting rail, for enclosures: (366 x 35 x 1)
EKIV 27	DIN-35 Mounting rail, for enclosures: (266 x 35 x 1)
EKIV 43 PL	Mounting plate, plastic, for enclosures:

Cover colour : Clear transparent

Gasket material : Polyurethane

Temperatures :

Temperature °C (short term) : -40 ... 120

Temperature °C (continuous) : -40 ... 80

Temperature °F (short term) : -40 ... 250

Temperature °F (continuous) : -40 ... 175

(370 x 270 x 2)

EKIV 43 Mounting plate, for enclosures:
(370 x 270 x 1)

FP A 43 Swing-out door/Front plate (aluminium), for
enclosures:
(268 x 368 x 1)

Rating :

Ingress protection (EN 60529): IP65;

Impact Resistance (EN 62262): IK08;

Electrical insulation : Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance : UL 508

Flammability Rating : UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C : 960 °C

NEMA Class

Certificates :

Certificate FI 40854