

# TPCM 111107



Sample image

**Order symbol :** TPCM 111107

**Product nr :** 5824021

**Description :** Enclosure, PC


**Remarks :** Grey cover

**EAN :** 6418074032065

**Including :**

**El. number :**

- Finland :
- Denmark :
- Sweden :



Dimensions :	Height	Width	Depth
mm :	110	110	65
inch :	4.33	4.33	2.56

**Accessories :**

FP 10674 Wall fastening lug (2 pcs) incl. screws

**Materials :**

Material : Polycarbonate  
 Base colour :  
 Cover colour :  
 Gasket material :

**Rating :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	-
Flammability Rating :	UL 746C 5"

**Temperatures :**

Temperature °C (short term) : -40 ... 120

Temperature °C (continuous) :

Temperature °F (short term) : -40 ... 250

Temperature °F (continuous) : -40 ... 175

Glow Wire Test (IEC 695-2-1) °C : 960 °C

NEMA Class

**Certificates :**

Certificate FI 40343