

CAB PCQ 604021 T



Sample image

Order symbol : CAB PCQ 604021 T

Product nr : 8113078

UL Code : 8143078

UL Name : UL CAB PCQ 604021T

Description : Cabinet, PC


Remarks : Smoked transparent cover

EAN : 6418074011121

El. number :

- Finland : 3421926
- Denmark :
- Sweden : 2540109

Including : Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



| Dimensions : | Height | Width | Depth |
|---------------------|---------------|--------------|--------------|
| mm : | 600 | 400 | 210 |
| inch : | 23.62 | 15.75 | 8.27 |

Accessories :

- EKIV 64H Mounting plate, for enclosures:
(570 x 370 x 1)
- PAT 12040 Hinge set

Materials :

| | |
|-------------------|----------------------|
| Material : | Polycarbonate |
| Base colour : | RAL 7035 -light grey |
| Cover colour : | Clear transparent |
| Gasket material : | Polyurethane |

| | |
|----------------|---|
| MB 12225 AL | Swing door set |
| EKIV 37 | DIN-35 Mounting rail, for enclosures: (366 x 35 x 1) |
| DRF 63/64 | DIN rail frame set, for enclosures: |
| FP A 64 | Swing-out door/Front plate (aluminium), for enclosures: (568 x 368 x 1) |

Temperatures :

| | |
|-------------------------------|-------------|
| Temperature °C (short term) : | -40 ... 120 |
| Temperature °C (continuous) : | -40 ... 80 |
| Temperature °F (short term) : | -40 ... 250 |
| Temperature °F (continuous) : | -40 ... 175 |

Rating :

| | |
|--|-------------------|
| Ingress protection (EN 60529): | IP66; IP67; |
| Impact Resistance (EN 62262): | IK08; |
| Electrical insulation : | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1 |
| UV resistance : | UL 508 |
| Flammability Rating : | UL 746C 5" |
| Glow Wire Test (IEC 695-2-1) °C : | 960 °C |
| NEMA Class | |

Certificates :

Certificate FI 40848