

CAB PCQ 303017 T



Sample image

Order symbol : CAB PCQ 303017 T

Product nr : 8113048

Description : Cabinet, PC



Remarks : Smoked transparent cover

EAN : 6418074011084

El. number :

- Finland : 3421922
- Denmark :
- Sweden : 2539184

Including : Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



Dimensions :	Height	Width	Depth
mm :	300	300	170
inch :	11.81	11.81	6.69

Materials :

Material : Polycarbonate

Accessories :

- EKIV 33 Mounting plate, for enclosures: (270 x 270 x 1)
- PAT 12040 Hinge set
- MB 12225 AL Swing door set
- FP A 33 Swing-out door/Front plate (aluminium), for enclosures:

Base colour : RAL 7035 -light grey
Cover colour : Clear transparent
Gasket material : Polyurethane

(268 x 268 x 1)

EKIV 27 DIN-35 Mounting rail, for enclosures:
(266 x 35 x 1)

DRF 33 DIN rail frame set, for enclosures:

Temperatures :

Temperature °C (short term) : -40 ... 120
Temperature °C (continuous) : -40 ... 80
Temperature °F (short term) : -40 ... 250
Temperature °F (continuous) : -40 ... 175

Rating :

Ingress protection (EN 60529): IP66; IP67;
Impact Resistance (EN 62262): IK08;
Electrical insulation : Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance : UL 508
Flammability Rating : UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C : 960 °C
NEMA Class

Certificates :

Certificate FI 40848