

CAB PC 203018 T



Sample image

Order symbol : CAB PC 203018 T

Product nr : 8113031

UL Code : 8143031

UL Name : UL CAB PC 203018 T

Description : Cabinet, PC, Smoked transparent door


Remarks : Latch on the short side

EAN : 6418074020031

EI. number :

- Finland : 3424153
- Denmark : 8212020414
- Sweden : 2539937

Including : Cabinet base. door with PUR gasket. latches. screws for mounting plate/ DIN-rail and corner plugs.



Dimensions :

	Height	Width	Depth
mm :	200	300	180
inch :	7.87	11.81	7.09

Materials :

Accessories :

MB 12225 AL	Swing door set
EKIV 27	DIN-35 Mounting rail, for enclosures: (266 x 35 x 1)
DRF 23	DIN rail frame set, for enclosures:

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	Clear transparent
Gasket material :	Polyurethane

FP A 23	Swing-out door/Front plate (aluminium), for enclosures: (168 x 268 x 1)
EKIV 17	DIN-35 Mounting rail, for enclosures: (166 x 35 x 1)
EKIV 23	Mounting plate, for enclosures: (170 x 270 x 1)

Temperatures :

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

Rating :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

Certificates :

Certificate FI 40854