

CAB PC 303018 T3B

FIBOX
Enclosing innovations



Sample image

Order symbol : CAB PC 303018 T3B

Product nr : 8113042

UL Code : 8143042

UL Name : UL CAB PC 303018 T3B

Description : Cabinet, PC, Smoked transparent door


Remarks : Lock on the long side

EAN : 6418074020154

El. number :

- Finland : 3424161
- Denmark : 8212019234
- Sweden : 2539943

Including : Cabinet base. door with PUR gasket. 3mm double bit lock(s) with key. screws for mounting plate/DIN-rail and corner plugs.



Dimensions :	Height	Width	Depth
mm :	300	300	180

Accessories :

EKIV 33 Mounting plate, for enclosures:
(270 x 270 x 1)

inch : 11.81 11.81 7.09

Materials :

Material : Polycarbonate
Base colour : RAL 7035 -light grey
Cover colour : Clear transparent
Gasket material : Polyurethane

Temperatures :

Temperature °C (short term) : -40 ... 120
Temperature °C (continuous) : -40 ... 80
Temperature °F (short term) : -40 ... 250
Temperature °F (continuous) : -40 ... 175

MB 12225
AL Swing door set

FP A 33 Swing-out door/Front plate (aluminium), for enclosures:
(268 x 268 x 1)

EKIV 27 DIN-35 Mounting rail, for enclosures:
(266 x 35 x 1)

DRF 33 DIN rail frame set, for enclosures:

Rating :

Ingress protection (EN 60529): IP65;
Impact Resistance (EN 62262): IK08;
Electrical insulation : Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance : UL 508
Flammability Rating : UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C : 960 °C
NEMA Class

Certificates :

Certificate FI 40854