

# PC 2828 13 T-2FSH

**FIBOX**  
Enclosing innovations



Sample image

**Order symbol :** PC 2828 13 T-2FSH

**Product nr :** 2539547

**Description :** Enclosure, PC


**Remarks :** Transparent hinged cover

**Including :** Base with screws for mounting plate. cover with PUR gasket and polyamide cover screws.

**EAN :** 6418074052841

**El. number :**

- Finland : 3435752
- Denmark :
- Sweden : 2539547



**Dimensions :**

mm :

**Height**

280

**Width**

280

**Depth**

130

**Accessories :**

EKOZR

Extension frame, for enclosures:  
(280 x 280 x 50)

inch : 11.02 11.02 5.12

**Materials :**

Material : Polycarbonate  
Base colour : RAL 7035 -light grey  
Cover colour : Clear transparent  
Gasket material : Polyurethane

**Temperatures :**

Temperature °C (short term) : -40 ... 120  
Temperature °C (continuous) : -40 ... 80  
Temperature °F (short term) : -40 ... 250  
Temperature °F (continuous) : -40 ... 175

EKV 22 DIN-35 Mounting rail, for enclosures:  
(235 x 35 x 1)  
EKOVT Mounting plate, for enclosures:  
(238 x 238 x 1)  
MPI EKO 2828 Multiperforated plastic mounting plate  
(244 x 244 x 4)

**Rating :**

Ingress protection (EN 60529): IP65;  
Impact Resistance (EN 62262): IK08;  
Electrical insulation : Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance : UL 508  
Flammability Rating : UL 746C 5"  
Glow Wire Test (IEC 695-2-1) °C : 960 °C  
NEMA Class

**Certificates :**

Certificate NCS FI 30308