

PRODUCT INFORMATION SHEET

Combination ratchet spanners with flex head







Description




Combination ratchet spanners with flex head ideal for loosening and tightening threaded joints ended with hexagonal, decagonal or torx-type element. No need to take the spanner off the nut to make another turn.

Characteristics

- made of high-grade chromium-vanadium alloy steel for corrosion protection
- 12-point ring, angled
- 72-tooth ratchet mechanism
- an open end angled at 15° for optimum access to fastening element
- flex head pivots and ensures operation within 0-90°
- durable
- matt

Technical data

	8 - 21 mm
	1 pc
	5 pcs
	alloy steel CrV6140

		
8 mm	HT1R048	5901867144645
9 mm	HT1R049	5901867144652
10 mm	HT1R050	5901867144669
11 mm	HT1R051	5901867144676
12 mm	HT1R052	5901867144683
13 mm	HT1R053	5901867144690
14 mm	HT1R054	5901867144706
15 mm	HT1R055	5901867144713
16 mm	HT1R056	5901867144720
17 mm	HT1R057	5901867144737
18 mm	HT1R058	5901867144744
19 mm	HT1R059	5901867144751
20 mm	HT1R060	5901867144768
21 mm	HT1R061	5901867144775

CrV

