

### Verderflex M60 OEM Panel Mounted Peristaltic pump

No.	Description	rotation speed	Hose inner diameter	Hose material	RS Stock No.
164.0001	M60NA 024DC192R 2R 040VP PBZZZ	192 U/MIN	4,0 mm	Verderprene	<b>185-6148</b>
164.0011	M60NA 024DC099R 2R 016VP PBZZZ	99 U/MIN	1,6 mm	Verderprene	<b>185-6137</b>
164.0012	M60NA 024DC099R 2R 032VP PBZZZ	99 U/MIN	3,2 mm	Verderprene	<b>185-6138</b>
164.0013	M60NA 024DC099R 2R 040VP PBZZZ	99 U/MIN	4,0 mm	Verderprene	<b>185-6139</b>
164.0014	M60NA 024DC099R 2R 048VP PBZZZ	99 U/MIN	4,8 mm	Verderprene	<b>185-6140</b>
164.0029	M60NA 024DC150R 2R 016VP PBZZZ	150 U/MIN	1,6 mm	Verderprene	<b>185-6142</b>
164.0030	M60NA 024DC150R 2R 032VP PBZZZ	150 U/MIN	3,2 mm	Verderprene	<b>185-6143</b>
164.0031	M60NA 024DC150R 2R 040VP PBZZZ	150 U/MIN	4,0 mm	Verderprene	<b>185-6144</b>
164.0032	M60NA 024DC150R 2R 048VP PBZZZ	150 U/MIN	4,8 mm	Verderprene	<b>185-6145</b>
164.0047	M60NA 024DC192R 2R 016VP PBZZZ	192 U/MIN	1,6 mm	Verderprene	<b>185-6146</b>
164.0048	M60NA 024DC192R 2R 032VP PBZZZ	192 U/MIN	3,2 mm	Verderprene	<b>185-6147</b>
164.0049	M60NA 024DC192R 2R 040VP PBZZZ	192 U/MIN	4,0 mm	Verderprene	<b>185-6149</b>
164.0126	M60NA 024DC192R 2R 048VP PBZZZ	192 U/MIN	4,8 mm	Verderprene	<b>185-6135</b>
164.0128	M60NA 024DC099R 2R 016SI PBZZZ	99 U/MIN	1,6 mm	Silicone	<b>185-6125</b>
164.0129	M60NA 024DC099R 2R 032SI PBZZZ	99 U/MIN	3,2 mm	Silicone	<b>185-6126</b>
164.0130	M60NA 024DC099R 2R 040SI PBZZZ	99 U/MIN	4,0 mm	Silicone	<b>185-6127</b>
164.0131	M60NA 024DC099R 2R 048SI PBZZZ	99 U/MIN	4,8 mm	Silicone	<b>185-6128</b>
164.0146	M60NA 024DC150R 2R 016SI PBZZZ	150 U/MIN	1,6 mm	Silicone	<b>185-6129</b>
164.0147	M60NA 024DC150R 2R 032SI PBZZZ	150 U/MIN	3,2 mm	Silicone	<b>185-6130</b>
164.0148	M60NA 024DC150R 2R 040SI PBZZZ	150 U/MIN	4,0 mm	Silicone	<b>185-6131</b>
164.0149	M60NA 024DC150R 2R 048SI PBZZZ	150 U/MIN	4,8 mm	Silicone	<b>185-6132</b>
164.0164	M60NA 024DC192R 2R 016SI PBZZZ	192 U/MIN	1,6 mm	Silicone	<b>185-6133</b>
164.0165	M60NA 024DC192R 2R 032SI PBZZZ	192 U/MIN	3,2 mm	Silicone	<b>185-6134</b>
164.0166	M60NA 024DC192R 2R 048SI PBZZZ	192 U/MIN	4,8 mm	Silicone	<b>185-6136</b>