


coupling socket NPHS-D6-M-G12

Part number: 8059277

FESTO



Data sheet

Feature	Value
Nominal size	10 mm
Operating pressure complete temperature range	-0.95 ... 20 bar
Standard nominal flow rate	2,000 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-20 ... 80 °C
Nominal tightening torque	25 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	200 g
Pneumatic connection, port 1	Male thread G1/2
Materials note	Conforms to RoHS