



P.C.B. LAYOUT

SCALE: 1:1

MATERIAL & FINISHES

INSULATOR - PBT GLASS FILLED UL94V-0
 CONTACT - BRASS
 SHELL - STEEL
 PLATING - CONTACT GOLD FLASH PLATED

ELECTRICAL CHARACTERISTICS

RATING CURRENT : 3A
 CONTACT RESISTANCE : $< 15m\Omega$
 INSULATION RESISTANCE : $< 3000M\Omega$ AC 500V
 DIELECTRIC VOLTAGE : 1000V / MIN
 OPERATING TEMPERATURE : $-50^{\circ}C$ TO $+105^{\circ}C$

Poles	Part No.	Dim A	Dim B	Dim C	Dim D	Dim E
9	DMR-9P	16.92	24.99	30.81	11.08	6.955
15	DMR-15P	25.25	33.32	39.14	19.39	6.965
25	DMR-25P	38.96	47.04	53.04	33.24	6.90
37	DMR-37P	55.42	63.50	69.32	49.86	6.82

TOLERANCE TABLE

.0	± 0.20
.00	± 0.10
.000	± 0.05

APPROVED:	DATE:	TITLE: DMR-XP 公头 铆合锁螺丝
CHECKED:	DATE:	
DRAWN: LYF	DATE: 2008-04-07	CLIENT P/N /
		UNIT mm
		SCALE free
		FILE NO. Ckmtw-DMR-0004
		REV. A

深圳市灿科盟实业有限公司
 CKMTW CHANKLEMENT INDUSTRYCO., LTD