




, MTG



- >>
- >>
- >>
- >>
- >>






	Yuasa		CCA,			
MT12-2,5	YTX4B-BS	2,5	40	=	113*38*86	0,91
MT12-2,6	YTX4A-BS	2,6	45	=	113*48*85	0,96
MT12-4	YB4L-B, YT4L-BS	4,0	50	(- +)	113*70*85	1,44
MT12-5	YTX5L-BS, YTZ7S, YT5L-BS	5,0	70	(- +)	113*70*105	1,83
MT12-5-A	12N5-3B, YB5L-B	5,0	75	(- +)	119*59*130	1,93
MT12-7	YTX7A-BS	7,0	90	(+ -)	150*87*93	2,55
MT12-7-A	YTX7L-BS	7,0	85	(- +)	113*70*131	2,50
MT12-8	YT7B-BS, YT9B-BS, YT7B-4	8,0	85	(+ -)	150*65*93	2,30
MT12-9	YTX9-BS, YTX9	9,0	120	(+ -)	150*87*105	3,05
MT12-9-A	YT9B-BS	9,0	115	(+ -)	150*70*105	2,83
MT12-10	YB9A-A, YB9-B, 12N9-4B-1	10,0	120	(+ -)	135*75*139	3,11
MT12-10-A	YTZ10S	10,0	190	(+ -)	150*88*93	3,20
MT12-11	YTZ12S, YTZ14S	11,0	230	(+ -)	150*88*110	3,91
MT12-12	YTX14-BS, YTX12-BS	12,0	180	(+ -)	150*87*130	3,99
MT12-12-A	YT12B-BS	12,0	175	(+ -)	150*70*130	3,63
MT12-12-B	YT14B-BS	12,0	210	(+ -)	150*69*145	4,16
MT12-14	YTX16-BS, YB16B-A	15,0	200	(- +)	150*87*145	4,46
MT12-14-A	YB14-A2, YTX14AH-BS, YB12A-	14,0	210	(+ -)	134*90*166	4,68
MT12-14-B	YTX14-BS, YTX14H-BS, YTX16-BS, YB16B-A	14,0	200	(+ -)	150*87*145	4,80
MT12-16	YB16AL-A2	16,0	250	(- +)	205*87*162	6,60
MT12-18	YTX20L-BS, YTX20HL-BS, YB16CL-B, YB16L-B, YB18L-A	18,0	270	(- +)	175*87*155	5,70
MT12-18-A	YTX20H-BS	18,0	230	(+ -)	150*87*161	5,07
MT12-18-B	YTX20CH-BS	18,0	270	(+ -)	150*87*161	5,64
MT12-18-C	YTX20-BS, YTX20H, YB16-B-CX, YB16-B, YB18-A	18,0	270	(+ -)	175*87*155	6,04
MT12-20	Y50-N18L-A, Y50-N18L-A3, YTX24HL-BS	21,0	350	(- +)	205*87*162	7,20
MT12-20-A	YT19BL-BS	20,0	310	(+ -)	175*87*155	6,01
MT12-20-B	YTX20L-BS, YTX20HL-BS, YB16L-B, YB18L-A	20,0	270	(- +)	175*87*155	5,70
MT12-30	YTX30L, YB30L-B, YTX30L-BS, BA30LSHDT	30,0	385	(- +)	166*126*173	9,68

G

NANO-GEL TECHNOLOGY



	Yuasa		CCA,			
MTG12-2,3	GT4B-5 (GEL)	2,3	40	=	113*38*85	0,92
MTG12-2,4	YTR4A-BS(GEL)	2,3	45	=	115*48*85	0,97
MTG12-4	YTX4L-BS(GEL), YTZ5S	4,0	50	(- +)	113*70*85	1,45
MTG12-5	YTZ7S(GEL)	5,0	70	(- +)	113*70*105	1,83
MTG12-6	YTX5L-BS(GEL)	6,0	70	(- +)	113*70*105	2,09
MTG12-7	YTX7A-BS(GEL)	7,0	90	(+ -)	150*87*93	2,57
MTG12-7-A	YTX7L-BS (iGEL)	7,0	85	(- +)	113*70*130	2,44
MTG12-8	YT7B-4 (GEL)	7,0	85	(+ -)	150*65*93	2,32
MTG12-9	YT9B-4 (GEL)	9,0	115	(+ -)	150*68*105	2,73
MTG12-9-A	YTX9-BS (iGEL)	9,0	120	(+ -)	150*87*105	3,07
MTG12-10-A	YTZ10S(GEL)	8,6	190	(+ -)	150*87*93	2,90
MTG12-11	YTZ14S(GEL)	11,0	175	(+ -)	150*69*130	3,58
MTG12-12	YT12B-4 (GEL)	12,0	175	(+ -)	150*87*110	3,58
MTG12-14	YT14B-4 (GEL)	14,0	210	(+ -)	150*69*145	4,18
MTG12-14-A	YTX14-BS (GEL)	14,0	200	(+ -)	150*87*145	4,48
MTG12-14-B	YB14L-BS (GEL)	14,0	210	(- +)	135*90*167	4,70
MTG12-16	YTX16-BS (GEL)	16,0	230	(+ -)	150*87*161	5,14
MTG12-18	YTX20L-BS, YB16CL-BS, YB16L-B, YB18L-A	18,0	270	(- +)	175 87 155	5,73
MTG12-20	YT20L-BS(GEL)	20,0	270	(- +)	175*87*155	5,73
MTG12-30	YB30L-B, YTX30LBS, YIX30L-BS, BA30LSHDT	30,0	385	(- +)	165*125*175	9,84