

## Coaxial Cable Connector 24\_SMC-50-2-110/111\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-9\_MIL-STD-348A/312\_CECC 22140



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	10 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0017 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
Crimp ferrule	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing	DOU-00008852
Catalogue drawing	DCA-00008854
Assembly instruction	DOC-0000179013
Mounting hole	DOU-00008855

### Ordering Information

Single package	24_SMC-50-2-110/111_NE
Bulk 100 pcs package	24_SMC-50-2-110/111_NH

### Additional Information

Suitable cables	RG_316_U, ENVIROFLEX_316, RG_188_A/U, RG_174_U
-----------------	--