


## Chloroprene tubing and grommets

### Helsyn TH - thin wall



Chloroprene tubing

TYPE	Supplied Ø D min.	Wall (WT)	Bundle Ø max.	Reel Length	Pack Cont.	Colour	Tools	Article-No.
TH100BKX25M	10.0	1.00	20.0	25 m	25 m	Black (BK)	37;39-40	608-01208
TH120BKX25M	12.0	1.00	23.0	25 m	25 m	Black (BK)	38-39;41	608-01209
TH140BKX20M	14.0	1.10	25.0	20 m	20 m	Black (BK)	38-39;41	608-01210
TH170BKX20M	17.0	1.20	28.0	20 m	20 m	Black (BK)	38-39;41	608-01202

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



TYPE	Supplied Ø D min.	Wall (WT)	Bundle Ø max.	Length (L)	Pack Cont.	Colour	Tools	Article-No.
TH100X35BK	10.0	1.00	20.0	35.0	100 pcs.	Black (BK)	37;39-40	600-02493
TH120X50BK	12.0	1.00	23.0	50.0	100 pcs.	Black (BK)	38-39;41	600-02495
TH140X50BK	14.0	1.10	25.0	50.0	100 pcs.	Black (BK)	38-39;41	600-02496
TH170X50BK	17.0	1.20	28.0	50.0	100 pcs.	Black (BK)	38-39;41	600-02497

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools						
	35	36	37	39	40	41
	NA-0/1	NA-1K/3	NA-4/5	VA2.5/5	VA2.5/5+8	VA2.5/5+18
	569	569	569	570	570	570

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.