

Item no.: 260-334  
 Product description: 4-CONDUCTOR TERMINAL BLOCK;  
 LATERAL MARKING; WITH MOUNTING  
 FEET 209-123 FOR TS 35; SIDE-ENTRY;  
 CAGE CLAMP®CONNECTION;  
 HORIZONTAL TYPE



Packing unit 300 6\*50 pieces

Cross section from [mm <sup>2</sup> ]	0,08 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	1,5 mm <sup>2</sup>
Cross section from [AWG]	28 AWG
Cross section to [AWG]	16 AWG
Connection method	CAGE CLAMP®CONNECTION
Number of strands	2
Voltage CSA	300 V
Voltage UL	300 V
Current UL	10 A
Current CSA	15 A
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	18 A
Weight	2,51 g
Color	blue
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	17 mm
Height	0,669 in
Width	8 mm
Width	0,315 in
Depth	25 mm
Depth	0,985 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in

	Admission office	Approval no.	Voltage [ V ]	Current [ A ]	Cross section [ mm <sup>2</sup> ]
260-334	BBJ	B/12/696/03	400	17,5	1,5
260-334	BV	07436/C0	400	17,5	0,08-1,5
260-334	CCA	DK96-00357	400	17,5	1,5
260-334	CSA	18677-45	300	15	24-16
260-334	DEMKO	120039	400	17,5	1,5
260-334	Dep.MaE	CS4590N	300	20	

260-334	DNV	E6998	400	17,5	1,5
260-334	GL	17295-00HH	400	17,5	1,5
260-334	KEMA	92.6446.01	500		1,5
260-334	KR	HMB05880-EL002	400	17,5	1,5
260-334	LR	91/20242(E3)	500	19,5	1,5
260-334	NEMKO	M59289/02	500		1,5
260-334	PRS	TE/1219/880590/98	400	17,5	1,5
260-334	RMR	99.00007.250	400	17,5	1,5
260-334	RosTesT	B09523	400	17,5	1,5
260-334	SEMKO	9408057	500		1,5
260-334	UL	E45172	300	10	28-16
260-334	VDE	207 ÜG,Bl.1	500		1,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected