



## DWE4206

1010W 115mm Slide Switch SAG No-Volt

### Selling Proposition

- No-volt release switch prevents the unit from starting unintentionally when locked on. Switch must be consciously reset before power is delivered
- Soft start reduces movement of the tool on startup increasing user control
- High efficiency motor design improves performance in demanding applications
- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking
- Small girth allow comfortable gripping resulting in superior ergonomics
- The low profile gear case allows access in confined areas

### Standard Equipment

- Protective keyless guard
- Multi-position anti vibration side handle
- Inner and outer disc flange
- Spanner

### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	1010 Watts
No Load Speed	11000 rpm
Max. Disc Diameter	115 mm
Spindle Thread	M14
Weight	2.1 kg
Length	285 mm
Height	80 mm
Hand/Arm Vibration - Grinding	8.3 m/s <sup>2</sup>