




DIN 7985 A

~ISO 7045

4.8

Standard withdrawn



BN 3334

Pozi pan head machine screws


form Z


Steel 4.8


zinc plated blue

- ~UNI 7687
- ~CSN 021147

i All lengths fully threaded

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
2096765	M2	4	1,72	1	2,4	1,1	1,35	3
1538438								4
1538446								5
1538454								6
1538462								8
1538470								10
1538489								12
3169928								16
2096773								20
2096781	M2,5	5	2,12	1	2,6	1,27	1,52	3
1538497								4
1538500								5
1538519								6
1538527								8
1538535								10
1538543								12
1538551								16
2096803								20
2096811								25
2096838								30
3056367	M3	6	2,52	1	3	1,68	1,93	3
1538578								4
1538586								5
1538594								6

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1538608	M3	6	2,52	1	3	1,68	1,93	8
1538616								10
1538624								12
1538632								(14)
1538640								16
5402876								(18)
1538659								20
1538667								25
1538675								30
1538683								35
1538691								40
2096846								45
2096854								50
2096862								60
3056368	M4	8	3,25	2	4,3	1,9	2,36	4
1538705								5
1538713								6
1538721								8
1538748								10
1538756								12
1538764								(14)
1538772								16
5402872								(18)
1538780								20
5402873								(22)
1538799								25
1538802								30
1538810								35
1538829								40
3092560								45
2096870								50
2096889								60
2096897								70
2096900								80
2096919								100
3056369	M5	10	3,95	2	5	2,64	3,1	5
1538837								6
1538845								8
1538853								10
1538861								12
1538888								(14)

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1538896	M5	10	3,95	2	5	2,64	3,1	16
1538918								20
1538926								25
1538934								30
1538942								35
1538950								40
5402878								45
1538969								50
2096927								60
2096935								70
2096943								80
2096951								100
3056371	M6	12	4,75	3	6,7	3,02	3,48	6
1538977								8
1538985								10
1538993								12
1539000								(14)
1539019								16
1539027								20
1539035								25
1539043								30
1539051								35
1539078								40
5402880								45
1539086								50
2096978								60
2096986								70
2096994								80
2097001								100
5402881	M8	16	6,15	4	8,8	4,06	4,52	16
5402882								20
5402883								25
5402884								30
5402885								40