




Length



WSW P/N	Jacket color	Length(mm)
AK672/2-1	Beige	1000±30
AK672/2-2	Beige	2000±50
AK672/2-3	Beige	3000±50
AK672/2-5	Beige	5000±50

Electrical test:

1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm max.
3. Insulator resistance: 10Mohm min.
4. Dielectric test: DC 300V



NO.	NAME.	Q'TY	SPECIFICATION
①	PE Bag	1	Clear Print black "MADE IN CHINA"+ "1PC"
①	TIE	1	White
②	Out jacket	6g	Beige(BG002) PVC-45P, Flammability class: VW-1
②	Out jacket	6g	Beige(BG002) PVC-45P, Flammability class: VW-1
②	Cable	1	Beige(BG002) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm, Flammability class: VW-1
②	CONN	1	USB 2.0 B Male Shell:Nickel Pin:G/F Insulator color: White, UL 94V-0
②	CONN	1	USB 2.0 A Male Shell:Nickel Pin:G/F Insulator color:White, UL 94V-0

RoHS compliant
Unit: mm

Scale	Free	Customer-No.
TOLERANCE		ASSMANN WSW-No. AK672/2-X
DIM	TOL	Drawing-No. ASS 7066 CA
		rev02
Angle	TOL	Replace Sheet



1	2	3	4	5	6	7
		Modification	Date	Name		
		① Update the drawing	26.01.2016	Amy		
		② Drawn	11.02.2014	Joanna		