






1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	B
1	2	3	4	5	6	7	C
1	2	3	4	5	6	7	D
1	2	3	4	5	6	7	E
1	2	3	4	5	6	7	F
1	2	3	4	5	6	7	G
1	2	3	4	5	6	7	H



Wire cross section

W/SW P/N	Length (mm)
A-PC1503-020030-1	2000±50
A-PC1503-030030-1	3000±50

NOTES:

Material:

- 1.SJT 3x16AWG(1.31MM²) VW-1, Shielded, 60°C 300V.
 - 2.Jacket Color: Black.
 - 3.E-Green, L-Black, N-White.
- Electrical Test:**
1. 100% Open & Short Testing.
 2. Insulation Resistance: 100MΩ(Min).
 3. Voltage: 500V DC/1Min.

RoHS compliant

Unit: mm

Scale	Free	Customer-No.	
TOLERANCE		Drawn	16.01.2019
		Approved	16.01.2019
		Segal	
		ASSMANN W/SW-No.	A-PC1503-xx0030-1
		Drawing-No.	ASS 8463 CA
		Replace	rev00
		Sheet	

