


PXMBNI08FPF08AFLM11002 Datasheet

Product Name // PXMBNI08FPF08AFLM11002



// Product Description:

- ⊞ Material=Metal
- ⊞ Pins=4
- ⊞ Max Rating=60Vac
- ⊞ Ingress Protection=IP67
- ⊞ Operating Temperature= -25Å°C to +85Å°C
- ⊞ Contact Resistance=5?
- ⊞ Insulation Resistance=>100M?
- ⊞ Mechanical Cycles=100 (min)

// General Information:

| | |
|------------------------|--|
| Product Display Title: | M8 Series Front Panel Mount Connectors |
| Product Family: | Circular Automation Connectors |
| Product Series: | M8 Series |
| Body Material: | Brass - Nickel Plated |
| Contact Type: | Socket Contact |
| Number Of Contacts: | 8 Contacts |



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)