



silencer U-3/8-20

Part number: 534224

FESTO

For reducing noise and avoiding contamination at the exhaust ports of pneumatic components.



Data sheet

| Feature | Value |
|------------------------------------|--|
| Assembly position | Any |
| Container size | 20 |
| Operating pressure | 0 ... 10 bar |
| Flow rate to atmosphere | 6,000 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Sound pressure level | 82 dB(A) |
| Ambient temperature | -10 ... 70 °C |
| Product weight | 29.6 g |
| Pneumatic connection | G3/8 |
| Material of silencer insert | PE |
| Materials note | Free of copper and PTFE Conforms to RoHS |