

LEDBHR7W

7W – 700lm LED Energy Saver Bulkhead Light

Features & Benefits

- Round LED Bulkhead Light
- A powerful and energy saving alternative to standard bulkhead lights
- Wide light diffusion pattern
- Robust die cast housing with tough polycarbonate lens suitable for industrial, commercial and home installations
- IP65 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class I
Operating Temperature	-10°C to +40°C
Ingress Protection Rating	IP65
Wattage	7
Beam Angle	120°
Energy Efficiency	Class G
Energy Usage	8.4KwH/1000H
Lumen output (lm)	700

Data sheet

LEDBHR7W

Light / LED Lighting

Colour Temperature (K)	5000
LED Type	SMD (On LED Plate)
Mounting Hole Centres (mm)	88
Multiple Unit Support	Yes
Cable Entry(s)	Back Entry, Side Entry (Lip In Housing)

General

Weight (g)	330
Height (mm)	153
Width (mm)	153
Depth (mm)	59
Body Construction	Polycarbonate (Front Cover), Aluminium (Body)
Product Colour	Silver
Accessories (Included)	Fittings
EAN Number	5012483012635
Guarantee Period	3 Years

Line Diagrams

