


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00024	Connector, dc plug, 5.5x2.1x123 mm, molding style, spring contacts	1	
2	30-00440	Wire, 2C TS, 16 AWG, UL2468, 300V, 80C, 4.8 mm, VW-1, PVC, 87A	1	
3	24-00003	Overmold, PVC	1	black



Wiring Diagram	wire color
50-00024	center black
	center stripe black
	sleeve black

Revision:	Date:	Description:	Prepared: AW <small>Digitally signed by AW Date: 2018-06-12 16:32:37 -07'00'</small>	Notes: RoHS compliant <small>Function test: no open, no short circuit, no intermittent</small>	TENSILITY	Size: A <small>tel 1.541.323.3228 fax 1.541.323.4202</small>
A	11/22/2016	Initial release	Verified: GL <small>Digitally signed by GL Date: 2018-06-12 16:40:33 -07'00'</small>	Dimensions are in millimeters.		
				Description: Cable, 6100 mm, 5.5x2.1x12 mm 50-00024 dc plug to stripped tinned, 16 AWG, 30-00440 wire	Part number: 10-02378	
				Tolerances: X: ± 0.5 mm X,Y: ± 0.3 mm X,YY: ± 0.05 mm	Scale: 1:1	Sheet 1 of 1