


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00574	Connector, USB A 2.0 Plug, molding style, 180°, nickel plated shell, black insulator	2	
2	30-00872	Wire, 4C, 1PR 28 AWG, 2C 26 AWG, UL2725, 30V, 80C, 4.3 mm, shielded, VW-1, PVC, 79A, USB 2.0	1	
3	24-00210	Overmold, plug, USB A, slim design for aluminum shell	2	PVC, black
4	55-00073	USB A plug aluminum shell, 13x13.5x5.9 mm	2	black



Wiring diagram	
50-00574	Wire Color
1	Red
2	White
3	Green
4	Black
Shell	Drain & Shield

**Notes:**  
Functionally equivalent components may be substituted

Revision: A	Date: 1/5/2018	Description: Initial release	Prepared: AG <small>Digitally signed by AG 11:57:19 -0800</small>	Notes: RoHS compliant	<h1>TENSILITY</h1> <p>tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com</p>
			Verified: LA <small>Digitally signed by LA Date: 2018.01.18 17:37:11 -0800</small>	Function test: no open, no short circuit, no intermittent	
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm XX: ± 0.3 mm XXX: ± 0.05 mm	Description: Cable, 2000 mm, 50-00574 USB A plug to same, 26/28 AWG, 30-00872 wire	Size: Part number: A 10-02327
					Scale: 1:1
					Sheet 1 of 1