

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190700040**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Ring Tongue Terminal for 18-22 AWG Wire

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-19902-011-001 (PDF) |
| Drawing (PDF) | Product Specification PS-19902-013-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-19902-009-001 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

General

| | |
|-------------------------|-----------------------------|
| Product Family | Ring and Spade Terminals |
| Series | <u>19070</u> |
| Crimp Quality Equipment | Yes |
| Overview | <u>Solderless Terminals</u> |
| Product Name | InsulKrimp |
| Type | Ring |
| UPC | 800753069022 |

Physical

| | |
|---------------------------|--------------|
| Barrel Type | Closed |
| Flammability | 94V-0 |
| Insulation | PVC |
| Material - Plating Mating | Tin |
| Net Weight | 0.581/g |
| Packaging Type | Bag |
| Stud Size | 5-6 (M3-3.5) |
| Wire Insulation Diameter | 3.70mm max. |
| Wire Size AWG | 18, 20, 22 |
| Wire Size mm ² | 0.35-0.80 |

Solder Process Data


| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

| | |
|--------------------|------------|
| Engineering Number | AA-232-06X |
|--------------------|------------|

Reference - Drawing Numbers

| | |
|-----------------------|---|
| Product Specification | PS-19902-009-001, PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing | SD-19070-003-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19070 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|---|------------------|
| PremiumGrade Hand Crimp Tool | <u>640010100</u> |
| Hand Crimp Tool | <u>640010300</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <u>640050100</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <u>640050300</u> |
| ServiceGrade Hand Crimp Tool | <u>640160036</u> |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION