



PRODUCTS ▾

MARKETS ▾

RESOURCES

COMPANY ▾

DISTRIBUTORS ▾

CONTACT US

Home / Markets / Construction / Pushbutton – 49-59111

Images are for representation purposes only.

Pushbutton – 49-59111

16MM PLASTIC SEALED PUSHBUTTON

SKU: 49-59111 / Categories: [All Products](#), [Construction](#), [Industrial](#), [Push Button](#)

Description	Additional information	Datasheet
Downloads	Stock Checker	

Additional information

Switch Type	<i>Pushbutton</i>
Switch Operation	<i>Momentary</i>
Actuator Type	<i>Round Button</i>
Actuator / Cap Color	<i>Black</i>
Case Color	<i>Black</i>
Contact Configuration	<i>SPDT-DB</i>
Operating Force (Nom)	<i>3N / 10.8ozf</i>
Contact Material	<i>Gold Plated</i>
Contact Voltage AC Nom	<i>250V</i>
Contact Voltage DC Max	<i>50V</i>
Contact Current AC Max	<i>10A @ 250V AC</i>
Contact Current DC Max	<i>100mA</i>
Illuminated	<i>Non Illuminated</i>
Illumination Color	<i>Not Applicable</i>
Illumination Voltage	<i>Not Applicable</i>
Switch Mounting	<i>Threaded Bushing</i>
Panel Cutout (H x W)	<i>16.1 x 14.9</i>
IP Rating	<i>IP67</i>
Legend	<i>Not Applicable</i>
Operating Temperature Range	<i>-35°C to +85°C</i>
Standards Met	<i>Not Applicable</i>
Mechanical Life	<i>1000000</i>
Electrical Life	<i>500000</i>
Product Series	<i>49-59</i>



ITW Switches USA

195 E Algonquin Road
Des Plaines, IL 60016
P. 800-544-3354

ITW Switches UK

Edgington Way, Sidcup, Kent,
DA14 5EF. United Kingdom
P. + 44 (0) 208 308 8000

Terms of Use

- Privacy Policy/GDPR
- Modern Slavery Act
- Terms & Conditions (North America)
- Terms & Conditions (EU)