

## **Product**

## **KRF 1025S**



KRF-1025S is a crimping tool for right angeled uninsulated connectors, 1.0 - 2.5  $\,\mathrm{mm}^2/\mathrm{AWG}$  18 - 14, B/F-Crimp.

- High strength, through hardened alloy steel construction
- Unique mechanism significantly reduces hand force requirement over competing crimping tools
- Versatile and easy to customize for right hand or left hand users.
- Non-slip pad holds tool in place when leveraging on a work surface
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability





Die profile

Crimp profile

TECHNICAL DATA Length: 204 mm/8.03" Width: 22 mm/0.87" Height: 76 mm/2.99"

**Weight:** 560 gr/1.23 lb **Wire size:** 1-2.5 mm<sup>2</sup> / AWG 18-

AWG 14

Crimp dimensions mm/mm<sup>2</sup>:

1,0 - 2,5 mm<sup>2</sup>

Crimp dimensions inch/AWG:

AWG 18 - 14

Connector: Uninsulated 90° angeled

open barrel connectors

Description: For uninsulated angeled open barrel cannoectors.

Life span, cycles: 50,000