

Product Name	Custom waterproof IP68 MG12 plastic nylon cable gland with shroud
Model Number	MG
Material	Nylon
Size	MG12
Usage	Lock Cable Tight
Certification	CE IP68 SGS
Protection Level	IP68
Feature	Seal Part Hold Cable Firmly
Cable Range	4.5~8
Fire Proof Level	UL94V-2
Thread O.D	12
Thread length	9
Function	Resistant to the water , dust, oil
Seal Material	EPDM

## PRODUCT INFORMATION

### Product Overview

Thread: Metric (Divided type)PG,G,and NPT thread


Materials:UL approved Nylon PA66(Flammability UL 94V-2)for A.C.E parts,(Accept to make flammability UL 94V-0);EPDM rubber for B.D parts,(Also accept to make super rubber:resist high temperature rubber, resist strong acid/alkali, etc).

Protection degree:IP68

Working temperature:-40°C to 100°C


Features:The claws and seals of excellent design,sealing nut have a "click"sound and re-open,can hold cable firmly and have a wider cable range.Resistant to salt water,weak acid,alcohol,oil,grease and common solvency.

Colours:Black(RAL9005),gray(RAL7035),other color available upon request.



## MG Type

Product Model	Applicable to cable	Thread diameter	Thread length	Wrench diameter
MG12	4.5~8	12	9	19
MG16	6~10	16	15	22
MG20	9~14	20	15	27
MG25	13~18	25	15	33
MG32	18~25	32	15	41
MG40	24~30	40	20	50
MG50	30~40	50	23	62
MG63	40~50	63	24	75

<b>MG Thicken Type</b> 加厚型  Rubber Ring 橡胶圈	Product Model	Applicable to cable	Thread diameter	Thread length	Wrench diameter
	MG12	3~5.3	12	9	19
	MG16	4~7	16	15	22
	MG20	6~11	20	15	27
	MG25	10~16	25	15	33
	MG32	15~22	32	15	41
	MG40	20~25	40	20	50
	MG50	26~32	50	23	62
	MG63	38~46	63	24	75

