

Note: This datasheet may be out of date. Please download the latest datasheet of GCM32EC7YA106KA03#from the official website of Murata Manufacturing Co., Ltd. en-GB/products/productdetail?partno=GCM32EC7YA106KA03%23 http://www.mura

## GCM32EC7YA106KA03#


"#" indicates a package specification code.



< List of part numbers with package codes > GCM32EC7YA106KA03K GCM32EC7YA106KA03L

# Appearance & Shape







Packaging	Specifications	Minimum Order Quantity
К	330Embossed Tape	4000
L	180Embossed Tape	1000

Mass (typ.)		
1 piece	110mg	
φ180mm Reel	168g	

1 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date. Please download the latest datasheet of GCM32EC7YA106KA03#from the official website of Murata Manufacturing Co., Ltd. http://www.murata.com/en-GB/products/productdetail?partno=GCM32EC7YA106KA03%23

## GCM32EC7YA106KA03#

"#" indicates a package specification code.

### Specifications

Length	3.2±0.3mm
Width	2.5±0.2mm
Thickness	2.5±0.2mm
Capacitance	10µF ±10%
Distance between external terminals g	1.0mm min.
External terminal size e	0.3mm min.
Operating Temperature Range	-55°C to 125°C
Rated Voltage	35Vdc
Size code in inch(mm)	1210 (3225M)
Capacitance change rate	±22.0%
Temperature characteristics (complied standard)	X7S(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

2 of 4

Attention 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






Note: This datasheet may be out of date Please download the latest datasheet of GCM32EC7YA106KA03#from the official website of Murata Manufacturing Co., Ltd. ctdetail?partno=GCM32EC7YA106KA03%23


GCM32EC7YA106KA03#


"#" indicates a package specification code.


#### Characteristic Data

The charts below may show another part number which shares its characteristics.









3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Attention




Note: This datasheet may be out of date Please download the latest datasheet of GCM32EC7YA106KA03#from the official website of Murata Manufacturing Co., Ltd. cts/productdetail?partno=GCM32EC7YA106KA03%23

### GCM32EC7YA106KA03#

"#" indicates a package specification code.





1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Attention

4 of 4