



HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808-0
fax: +49 (0) 6402/808-60
email: info@hahn-trafo.de

Data sheet: BV EI 382 1194

| Frame size/Core height | Output (ta 70/B) | h 1 (mm) | h 2 (mm) | weight kg |
|------------------------|------------------|----------|----------|-----------|
| EI 382 / 13,5 mm | 4,5 VA | 23,1 | 28,1 | 0,150 |

- non short-circuit-proof at temperature class ta 70 °C/B
- **excellent function at thermal changes, vacuum casted**
 - maximum safety and long-term durability
- **with VDE-, ENEC 10-, UL-, and CSA certificates**
 - minimum size, maximum capacity
- **self-extinguishing cast housing and sealing material**
 - individually tested with certificate


| Article no. BV | Leistung VA | prim.V | Connecting pins | Operating point sec. $\pm 5\%$ | Connecting pins | No-load voltage V $\pm 5\%$ |
|----------------|-------------|--------|-----------------|-----------------------------------|-----------------|--------------------------------|
| EI 382 1194 | 4,5 | 230 | 1-5 | 2x15 V 150 mA | 6-7/9-10 | 21,2/21,2 |

Primary protection by means of transformer hegt coils to IEC 127 standards or secondarily with PTC resistances.

Certificates



Type "0" cast housing without fixing straps



Dimensions of drawing without tolerances $\pm 0,3$ mm. soldering pins 0,6 x 0,8 mm