



RE524-HP

- SRBP paper FR2 1.50 mm
- Single-sided 35 µm Cu
- Organic soldering protection (OSP)
- Hole spacing 2.54 x 2.54 mm
- 36 continuous strips with 61 holes
- Hole diameter 1.00 mm
- Connector 32-channel DIN 41612 grid 5.08 mm type D
- Size 100 x 160 mm