

WX2

2-Channel Power Unit, 200 W (255 W)
Product no.: WX2N



Benefits

- › Innovative operation concept
- › Robust touch screen with ESD safe glass
- › Intuitive use with turn-click-wheel with enter key and finger guide.
- › Blue LED backlighting
- › Multilingual menu navigation
- › High functionality
- › No safety rest with Stop & Go function needed thanks to integrated acceleration sensor
- › Optimized precision, better stability by sensor in the soldering iron
- › Specific parameterization of tool by storage medium in hand piece
- › Visual process control via blue LED ring light



Technical Data

Dimensions L x W x H (mm)	174 x 154 x 135
Dimensions L x W x H (inches)	6,85 x 6,06 x 5,31
Weight (approx.) in kg	3.45
Voltage	120 V
Power	200 W (255 W)
Channels	2
Temperature range (depends on tool) °C	100 - 550
Temperature range (depends on tool) °F	210 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3,5 mm pawl socket on back of device
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---