

Model: DXYD5090N-A



TYPE	UNIT	DXYD5090N-A
Rated Impedance	Ω	$8 \pm 15\%$
Rated (Max.) Power	W	0.5 (1.0)
Resonance Frequency	Hz	250
Rated Freq. Range	Hz	200~5000
Sound Pressure Level	dB	80 ± 2

