



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCKMR XCKVR XCRB XCRA
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 200 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRB12 XCRA15 XCRB55 XCRA12 XCRA51 XCRB52 XCKMR54D1H29 XCKMR24SR1H29 XCRA55 XCRA52 XCKMR54D2 XCRB51 XCKVR44D2H29 XCRB11 XCKVR24SR1H29 XCKVR54D1H29 XCKVR54D2H29 XCKMR54D2H29 XCRA11
-----------------------------	---

XCKVR44D1H29
XCRB15
XCKMR44D1H29
XCKMR54D1
XCKMR44D2H29

Net weight	0.019 kg
------------	----------

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------
