

M12 adaptor on top of MSUD valve plug form A 18mm

Form A (18 mm) – M12, connector top entry
24 V AC $\pm 20\%$ / DC $\pm 25\%$
LED and suppression
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.



[Link to Product](#)

Illustration




Female

Male



Depth: 27 mm



Product may differ from Image

Approvals**Form**

Form 41301

Technical Data

Operating voltage	24 V AC \pm 20% / DC \pm 25%
Rated surge voltage	0.8 kV
Operating current per contact	max. 4 A
Configuration	2 contacts + bridged PE
Locking of ports	M3/M12 \times 1 mm (recommended torque 0.4/0.6 Nm)
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range -25...+85 °C

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879144704
eClass	27143423
Packaging unit	1