

## M12 ADAPTOR ON TOP OF MSUD VALVE PLUG FORM A 18MM

Form A (18 mm) – M12, connector top entry  
24 V DC  $\pm 25\%$   
for pressure switches  
LED (yellow/green)  
5-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.




### [Link to Product](#)

Illustration




Female

Male



Depth: 27 mm



Product may differ from Image

**Approvals**

**Form**

Form 41321

**Technical Data**

Operating voltage	24 V DC $\pm 25\%$
Rated surge voltage	0.8 kV
Operating current per contact	max. 4 A
Configuration	3 contacts + PE
Locking of ports	M3/M12 $\times$ 1 mm (recommended torque 0.4/0.6 Nm)
Protection	IP67 inserted and tightened (EN 60529)

**General data**

Temperature range -25...+85 °C

**Commercial data**

country of origin	CZ
customs tariff number	85366990
EAN	4048879144681
eClass	27143423
Packaging unit	1