

## **SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE**



24V LED+Z-Diode PG9

Form A (18 mm)  
LED and Z-diode  
24 V AC  $\pm 20\%$  / DC  $\pm 25\%$   
PG9


Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

Illustration



Height: 41 mm



Product may differ from Image

**Form**

Form 29021

**Technical Data**

|                               |  |
|-------------------------------|--|
| Operating voltage             | 24 V AC $\pm 20\%$ / DC $\pm 25\%$     |
| Operating current per contact | max. 4 A                               |
| Configuration                 | 2 contacts + PE                        |
| Locking of ports              | M3 (recommended torque 0.4 Nm)         |
| Protection                    | IP65 inserted and tightened (EN 60529) |

**General data**

|                   |              |
|-------------------|--------------|
| Temperature range | -20...+60 °C |
|-------------------|--------------|

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | CN            |
| customs tariff number | 85366990      |
| EAN                   | 4048879187657 |
| eClass                | 27279221      |
| Packaging unit        | 1             |