

## **SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE**



24V LED+Z-Diode M16x1.5

Form A (18 mm)  
24 V AC  $\pm 20\%$  / DC  $\pm 25\%$   
LED and Z-diode  
metric


Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

Illustration



Height: 41 mm



Product may differ from Image

**Form**

The information in this brochure has been compiled with the utmost care.  
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 01/20

Form 29001

**Technical Data**

Operating voltage	24 V AC/DC
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Locking of ports	M3 (recommended torque 0.4 Nm)
Protection	IP65 inserted and tightened (EN 60529)
Tightening torque (clamp screw)	0.1 Nm
Sealing range (cable Ø)	5...10 mm

**General data**

Temperature range	-20...+60 °C
-------------------	--------------

**Commercial data**

country of origin	CN
customs tariff number	85366990
EAN	4048879187688
eClass	27279221
Packaging unit	1