



**SVS ECO VALVE PLUG FORM A 18MM 230V**

2+PE field-wireable M16x1.5


Form A (18 mm)  
250 V AC/DC  
without components  
metric  
field-wireable

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**



Height: 31 mm



Product may differ from Image

**Approvals**

EAC

ChinaRoHS25

**Form**

Form 29245

**Technical Data**

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 10 A
Configuration	2 contacts + PE
Connection cross section	0.5...1.5 mm <sup>2</sup>
Sealing range (cable Ø)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16×1.5 mm
Contact figure	Cable outlet can be turned in 90° steps
Protection	IP65 inserted and tightened (EN 60529)

**General data**

Temperature range	-40...+90 °C
Material (gasket)	NBR
Mounting method	inserted, tightened

**Commercial data**

country of origin	HU
customs tariff number	85366990
EAN	4048879187527
eClass	27279221
Packaging unit	1