

SVS ECO VALVE PLUG FORM A 18MM 230V



3+PE field-wireable M16x1.5

Form A (18 mm) for pressure switch
250 V AC/DC
without components
metric
field-wireable


Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Height: 31 mm



Product may differ from Image

Approvals

EAC

ChinaRoHS25

Form

Form 29405

Technical Data

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 10 A
Configuration	3 contacts + PE
Connection cross section	0.5...1.5 mm ²
Sealing range (cable Ø)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16×1.5 mm
Contact figure	Cable outlet can be turned in 90° steps
Protection	IP65 inserted and tightened (EN 60529)

General data

Temperature range	-40...+90 °C
Material (gasket)	NBR
Mounting method	inserted, tightened

Commercial data

country of origin	HU
customs tariff number	85366990
EAN	4048879187435
eClass	27279221
Packaging unit	1