

MNX ABS 95/75 HG



Order symbol: ABS 95/75 HG
Product nbr: 6081332
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074054722
El. number:
Finland 3421382
Denmark 8212023990

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	L	W	H	Rating:
mm:	100	100	75	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:	3.9	3.9	3	

Materials:	
Material:	ABS
Gasket material:	Polyurethane
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey

Temperatures:	
Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:	
MIV 95	Mounting plate (Galvanized steel)
MIN 8	DIN-15 Mounting rail
B-3	DIN-35 Mounting rail
FP 22046	Wall fastening lug (4 pcs)

Certificates:
Fimko
Europe EN 50298: 1998
Gost R

