


RECOMMENDED P. C. B LAYOUT (TOP VIEW)  
GENERAL TOLERANCE ±0.05

Specification:


- Electrical Characteristics:  
Contact Current Rating: 0.5 Amperes.  
Dielectric Withstanding Voltage: AC500V r.m.s  
Insulation Resistance: 1000 MΩ Minimum  
Contact Resistance: 40mΩ Maximum
- Environmental:  
Operating Temperature: -20°~+60°

3. MAJOR DIM: ▼  
WITHOUT CARD, SWITCH OPENED IN THE CONNECTOR;  
WHEN CARD PUSHED-IN, SWITCH WAS CLOSED



Pin No.	NAME	TYPE
1	DAT 2	I/O/PP
2	CD/DAT 3	I/O/PP
3	CMD	PP
4	VDD	S
5	CLK	I
6	VSS	S
7	DAT0	I/O/PP
8	DAT1	I/O/PP

ITEM	PART NAME	P/N	Q'TY	MATERIAL
①	TF01 Housing	TF01H-10-001	1PCS	LCP 473i Black
②	TF01 Contact	TF01S-10-001	1SET	C5191R-EH T=0.15mm
③	TF01-*1-4000 Shell	TF01S-10-002	1PCS	SPCC T=0.15mm
	TF01-*1-4001 Shell	TF01S-10-002	1PCS	C2680R-H T=0.15mm



## 深圳市华宇创精密电子有限公司

<p><b>TOLERANCE:</b> X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'</p> <p>UNIT: mm [inch]</p> <p>SCALE: 1:1 SIZE: A4</p>	<p><b>DRAWN BY :</b> 陈一鸣</p> <p><b>CHECKED BY:</b> 马跃</p> <p><b>APPROVED BY:</b> 邱敏</p>	<p><b>DATE :</b> 2014-02-23</p> <p><b>DATE :</b> 2014-02-23</p> <p><b>DATE :</b> 2014-02-23</p>	<p><b>PART NAME:</b> TF NO PUSH 外焊 (改后)</p> <p><b>PART NO.</b> HYCW110-TF10-180B</p> <p><b>MOLD NO.</b></p> <p><b>DRAW NO:</b> HYC-2108021310</p> <p><b>SHEET NO.</b> 1 OF 1</p>
---	---	---	--