


342106-1 Terminals and Splices
Ring and Spade Tongue Terminals



Line art represents typical product only.

<i>Searchable Features:</i>	
Terminal Shape	Ring Tongue
Body Style	PLASTI-GRIP
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Wire Range	22-16 [0.25-1.60 ²] AWG [mm]
Insulation	Yes
Insulation Support	Non-Insulation Support
Insulation Diameter	.140 [3.56] Max. in. [mm]
Stud Size	5/16 [M8]
Stud Diameter	.327 [8.30] in. [mm]
Shape	RING-043
Heavy Duty	Standard
Packaging Method	Loose Piece
Material	Copper
Finish	Tin
<i>Other Properties:</i>	
Dim. C	.437 [11.10] in. [mm]
Dim. L	1.059 [26.90] Max. in. [mm]
Dim. W	.469 [11.90] in. [mm]
Tongue Material Thickness	.032 [0.81] Max. in. [mm]
Color	Red
Insulation Material	Vinyl
Insulation Sleeve Material	PVC
CERTI-CRIMP Hand Tool	47386-4, 525690-0 (Great Britain Tool)